Distributed by:



## www.Jameco.com + 1-800-831-4242

The content and copyrights of the attached material are the property of its owner.



### Jameco Part Number 120221

#### **Silicon NPN Epitaxial Planar Phototransistors**

**Applications:** Detector in electronic control and drive circuits

#### **Features:**

· Hermetically sealed case

· BPW 76 - flat window, BPW 77 - lens

· Suitable for visible and near infrared radiation


• Exact central chip alignment typ.:±50 μm


BPW 76-Long range light barrier with an additional optics

Base terminet is available

Selected in groups

· Higher IR sensitivity





Angle of half sensitivity
BPW 76 ±q = 40°
BPW 77 ±q = 7.5°
Collector connected with case
~ JEDEC TO 18
~ 18A3 DIN 41876
~ JEDEC TO 18

#### Dr. v. //

Absolute maximum ratings			
Collector-base voltage	V <sub>cao</sub>	80	. v
Collector-emitter voltage	V <sub>CEO</sub>	70	V
Emitter-base voltage	VESO	5	V
Collector current	'c	50	mA
Peak collector current $\frac{t_p}{T} = 0.5, t_p \le 10 \text{ ms}$	I <sub>CM</sub>	100	mA
Total power dissipation  T <sub>amb</sub> ≤ 25 °C	P <sub>tot</sub>	250	mW
Junction temperature	$r_{i}$	125	°C
Storage temperature range	Teta	-55+125	°C


## BPW 76 · BPW 77




						•
Thermal resistance			Min.	Түр.	Max.	
Junction ambient		RINJA			400	K/W
Junction case		RING			150	K/W
Optical and electrical characte  T <sub>amp</sub> = 25 °C	ristics					
Collector dark current $V_{CE} = 20 \text{ V}, E = 0$		CEO		10	100	n.A
Collector light current $V_{CE} = 5 \text{ V, } E_A = 1 \text{ klx}^{13}$	*					
	BPW 76 A BPW 76 B	/c.		1.0		m/
	BPW 77 A BPW 77 B	/c.		15		m/ m/
$V_{CE} = 5 \text{ V, } E_{\bullet} = 1 \text{ mW/cm}^2$	$\lambda_{p} = 950  \text{nm}$					
	BPW 78 A BPW 78 B	/ce-1	0.4	0.6 1.2	0.8	m/
	BPW 77 A BPW 77 B	100	7.5 10	10	15	m
Peak wavelength sensitivity		λ <sub>p</sub>		800		nn
Range of spectral bandwidth	(50%)	λ <sub>0.6</sub>		6001050		nn
Collector-emitter breakdown / <sub>C</sub> = 1 mA	voltage	V(BR)CEO*)	70		8.5	
Collector-emitter saturation of Egraf mW/cm²,/c = 0.1 mA	BPW 76 BPW 77	VCEs at .		0.15 0.15	0.3	
Cut-off frequency $I_c = 5 \text{ mA}, V_s = 5 \text{ V}, R_L =$	100 Ω	1 <sub>e</sub>		110		kH
Capacitance, collector-emitte $V_{CE} = 5 \text{ V, } I = 1 \text{ MHz, } E = 0$		C <sub>CEO</sub>		7.5		p
Switching characteristics $V_s = 5 \text{ V, } I_c = 10 \text{ mA, } R_c = 10 \text{ mA}$	= 10 <b>9</b> Ω, see tes	st circuit				8
Delay time		t <sub>d</sub>		2.5		μ
Rise time		t,		3.5		μ
Turn-on time		f <sub>on</sub>		6.0		H
Storage time		1.		0.3		
Fall time		r,		3.2		
Turn-off time		toff		3.5		,


<sup>\*1</sup> AQL = 0.65 %






Test circuit








### **BPW 76 · BPW 77**






















# BPW 76 · BPW 77



